

REXNORD® AEROSPACE REXLON 2000® SELF-LUBRICATION LINER MATERIAL

Get an excellent bearing surface with Rexlon 2000 Self-lubrication Liner Material.

Rexnord offers two types of Rexlon 2000 Self-Lubrication Liner Material surface treatments: Rexlon 2000 LF and Rexlon 2000 Type III. These surface treatments are designed to protect your surface areas, such as bearings and other load-carrying moving components, from corrosion, fretting and galling.

Rexlon 2000 Type III can be applied to most metallic and some non-metallic surfaces of varying shapes due to its ability to be sprayed or molded, providing an excellent bearing surface for complex surface profiles. It is machineable and honeable after application for ultimate customization and pin to wear surface fit.

Rexlon 2000 LF is ideal for surface areas requiring low friction and wear. It provides excellent wear properties at low temperature for track rollers, hinge pins, cruciforms and other load-carrying moving components requiring low friction and wear.

Rexlon 2000 LF and Rexlon 2000 Type III provide you with:


- Fully machinable
- Minimal wear at high loads
- Can be applied to irregular shapes and most materials
- Low friction at cold temperature
- Exceeds the performance requirements of current military specifications

Rexlon 2000 LF applications

- **Airframe** — fixed wing (actuators, control rods, flight control hinge pins and strut sleeves), doors
- **Cargo rollers** — track rollers, cam followers
- **Energy systems** — steering linkages
- **Thrust bearings** — butterfly valves

Rexlon 2000 Type III applications

- **Airframe** — fixed wing (landing gear actuators, control rods), rotary wing (swash plates), flight controls, doors
- **Jet engines** — engine controls
- **Industrial machinery** — toggle mechanisms, butterfly valves
- **Off-road vehicles** — steering linkages, thrust bearings
- **Cargo handling** — cargo rollers
- **Railroads** — hand brakes and couplers
- **Energy systems** — stationary engine controls
- **Exercise and leisure products** — pivot joints



Rexnord Aerospace Bearing Applications

For decades, Rexnord Aerospace has been engineering bearing solutions for customers' application needs. By continually enhancing the technology and design of our bearings, we are able to apply innovation to challenging new and existing applications, including:

- Military, fixed and rotary wing aerospace vehicles
- Airframes
- Landing gear
- Power plants
- And more!

Every bearing is the result of advanced computer-aided design, exhaustive and comprehensive in-house testing, and state-of-the-art manufacturing methods. Our focus on technology allows us to meet unique requirements with high-quality bearings at reasonable costs.



REXNORD® AEROSPACE REXLON 2000® SELF-LUBRICATION LINER MATERIAL

Performance Characteristics

	Rexlon 2000 LF	Rexlon 2000 Type III
Dynamic Stress	25,000 psi	50,000 psi
Static Limit Stress	60,000 psi	80,000 psi
Static Ultimate Stress	90,000 psi	120,000 psi
Surface Speed	Up to 10 fpm	Up to 24 fpm
Nominal Thickness	0.010 to 0.015 in	0.010 to 0.015 in
Maximum Thickness	0.050 in	0.050 in
Wear	<0.002 in @ 25,000 psi load, +/- 25° of oscillation angle and 25,000 cycles	<0.001 in @ 50,000 psi load, +/- 25° of oscillation angle and 25,000 cycles
Operating Temperature	-67°F to +250°F (depending on surface speed and load)	-65°F to +440°F (depending on surface speed and load)
Coefficient of Friction	0.02 to 0.18 (at operating temperatures under 1,450 psi to 14,500 psi)	0.03 to 0.20, depending on load, motion, temperature and contaminant

Typical Product Properties

	Rexlon 2000 LF	Rexlon 2000 Type III
Hardness (Rockwell M Scale)	80–100	100–110
Color and Appearance	Dark gray through green-brown	Dark gray through green-brown
Density	0.05 lb/in ³	0.054 lb/in ³
Specific Gravity	1.4	1.5

Rexlon 2000 LF and Rexlon 2000 Type III are resistant to:

- Skydrol 500B-4
- MIL-H-5606
- MIL-L-7808
- JP-4
- BMS 3-33
- MIL-H-83282
- MIL-A-8243
- Hyjet IVA+
- TT-S-735 (type VII)
- Water

Applicable product specifications:

- Meets and exceeds the requirements of AS8943 (Rexlon 2000 LF)
- Meets and exceeds the requirements of Track Roller Specification BPS-B-173 (Rexlon 2000 LF)
- Qualified to SAE AS81934 (Rexlon 2000 Type III)
- Qualified to SAE AS81820 (Rexlon 2000 Type III)
- Qualified to Boeing BMS 3-39 (Rexlon 2000 Type III)



Motion Control Solutions Regal Rexnord

Contact us: aerospace.rexnord.com/contact

regalrexnord.com

The proper selection and application of products and components, including assuring that the product is safe for its intended use, are the responsibility of the customer. To view our Application Considerations, please visit <https://www.regalrexnord.com/Application-Considerations>.

To view our Standard Terms and Conditions of Sale, please visit <https://www.regalrexnord.com/Terms-and-Conditions-of-Sale> (which may redirect to other website locations based on product family).

"Regal Rexnord" is not indicative of legal entity.

Regal Rexnord, Rexnord Aerospace and Rexlon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

© 2013, 2022 Regal Rexnord Corporation, All Rights Reserved.
MCSSP22011E • Form# AR5-010

Since 1946, Rexnord Aerospace has satisfied the needs and critical demands of the aerospace industry with exceptional, high-quality products and innovative engineering. Choose Rexnord Aerospace products and solutions for your designs. Speak with our engineering sales staff to address your questions and design inquiries.

